

130mm

105mm

FCC Statement

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

This device complies with part 15 of the FCC rules. Operation is subject to the following two conditions (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

USER MANUAL

Please read this instruction carefully before operating

SPECIFICATIONS

- High precision strain gauge sensors
- Capacity: 0.1~150kg(0.2~330lb)
- Division: 0.05kg/0.1lb
- Auto sleep on/ Auto off
- Low battery/Overload indication
- Unit: kg / lb
- Power: 3xAAA batteries
- Working temperature: 5~40°C
- Size: (280*280*25mm)

Regular weighing

- Put the scale on a hard and flat floor. To ensure accuracy, please don't use this product on a carpet or other soft surfaces.
- Stand on the scale to start weighing.
- Stand still, then the scale will show your weight on the screen.
- To save power, the scale will automatically turn off in about 8 seconds if no action is taken.
- This product is designed for continuous weighing. You can continuously weigh before it turns off.

TOLERATE

0.1-2Kg±0.00Kg;	2-5Kg±0.05Kg	5-50Kg ±0.1Kg;
50-100Kg ±0.2Kg;	100-150Kg ±0.3Kg;	150-182.5Kg ±0.5Kg

Maintenances

- The four feet of the scale are rubber components, don't keep the scale loaded for a long time. This may damage the weight sensors and the scale will not be accurate.
- Do not put anything on the scale if not in use. This will consume the power and reduce the lifetime of batteries.
- Keep the product clean and dry; Keep it away from water; Avoid slipping or damaging the inside electric circuits when weighing.
- Do not drop the product; Avoid the risk of damaging the scale or breaking the glass. When the scale shows "Lo" it is running low on power. Please change the batteries immediately. Batteries may be permanently damaged if the scale is kept in low power mode for a long time.
- This product is a bathroom scale, for body weighing only; Please don't use it for commercial purposes.

INDICATION SYMBOL

Low Power Indication: 3.3V ± 0.2V display "Lo"

Overload Indication: Over the max weight 182.5kg / 405.5lb, then display Err

1

2