




Feature	
MovFast item	Parameters
Dimensions	161mm x 147 mm x 68.5 mm
Weight	~36g
Operating Temperature	-20°C ~ +60°C
Humidity	5%-95% Non-condensing
Drop Resistance	6 side * 30times drops for 1.5m
Ingress Protection	IP65
Sensors	Acceleration sensor, light sensor, and proximity sensor, E-Compass, Gyroscope, more than 10 hours.Support continuous scanning more than 24,000 times
Runtime	
Processor	MTK high-performance 8 cores 4*A53@2.0GHz+4*A53@1.5GHz
OS	Android 11
Wi-Fi	IEEE 802.11 a/b/g/n/ac
Resolution	480*800

Software	
	The application of scanning and decoding. Effectively recognizing, outputting the corresponding code, verification information
	MovStage helps users easily batch configure multiple PDA devices, with installing applications, configuring setting and Kiosk application etc functions. This tool increases efficiency, reduces repeat work and errors in manual operations.
	Provide the user with a dedicated, functionally limited single application mode. Limit PDA devices to workstations dedicated to a specific application. Provide the user with a tool that provides security, privacy and ensures that the user is focused on a specific application.

Notice	
Safety	*Charging Connect the device with the plug or the socket according to the connector to prevent damage to the connector due to the mismatched plug or the power adapter; To avoid injury, unauthorized person shall not open the power adapter; This product may cause radio interference in living environments. In that case, the user may be required to take adequate measures against interference. Significant Safety Instructions * Do not install or use the device during lightning storm in order to avoid the potential risks of lightning shock; * To avoid the damages of eyes and safety, Do not Aim or Align Scanner with eyes; * Please turn off the power immediately if you notice abnormal odor, heat, or smoke; Suggestions * Do not use the device near water or moisture to prevent liquid from falling into the device; * Do not use the device in extremely cold or hot environments, such as near flames or lit cigarettes; * Do not drop, throw or bend the device; * Use the device in a clean and dust-free environment if possible to prevent small items from falling into the device; * Please do not use the device near medical equipment without permission; * The operating temperature should be 20°C~60°C.

PRODUCT SAFETY WARNINGS	
PRODUCT SAFETY WARNINGS	To prevent possible injury, please read all instructions and safety information before you use the product. Operating temperature: -20°C ~ 60°C Storage temperature: -40°C ~ 70°C Battery & Safety • Charge battery only at ambient temperatures ranging from 0°C to 40°C. • Please do not attempt to repair, disassemble or modify the battery. Do not place or use battery near fires, heaters, direct sunlight, or other heat sources. Prolonged exposure to heat may cause battery leakage, explosions, or fires. • Please do not place pressure on or pierce the battery with hard objects.Damaging the battery could cause battery leakage, overheating, or fires. • Battery liquid may cause damage to skin or clothes. If exposed, immediately wash skin with water and seek medical attention. • If you experience any battery abnormalities, such as high temperature, discoloration, distortion, or leakage, immediately discontinue usage of the device and contact customer support. • If the battery's internal liquid comes in contact with your eyes, rinse thoroughly and immediately seek medical attention. • Do not connect your device to a high-voltage power supply or the battery could become damaged. • All batteries have a limited lifespan and will begin to lose capacity after several hundred charges/discharges. • Do not dispose of the battery as household waste. Please refer to local regulations.

PRODUCT SAFETY WARNINGS	
	The equipment meets the requirements of the relevant regulations and standards of the European Economic Area.CE marking is a harmonized certification system set up by the European Union in order to ensure that products meet the basic requirements for safety, health and the environment during their free circulation and sale in the European market. The device has been tested and evaluated by the Federal Communications Commission (FCC) and complies with the relevant radio spectrum and electromagnetic compatibility requirements in the U.S. FCC certification ensures that the device is legal for sale and use in the U.S..
	Ranger1 K/G Quick Start Guide MOVFAST

Radio Waves spec		
Radio	Frequency	Max Output Power (dBm)
GSM	900MHz	-32.0
	1800MHz	-26.9
WCDMA	FDD 1	-22.64
	FDD 3311	-22.41
E-UTRA FDD	FDD 1	-22.79
	FDD 3	-23.06
	FDD 7	-22.77
	FDD 8	-23.59
	FDD 20	-23.28
	TDD 36	-22.56
E-UTRA TDD	TDD 38	-23.03
	TDD 40	-22.87
RTE(Losses)		-15.1
BER		-3.7
WiFi(2.4-G)		-17.0
WiFi 5G Band 1		-16.9
WiFi 5G Band 2		-17.1
WiFi 5G Band 4		-13.9

BE BG CZ DK HU MT
DE EE IE EL NL AT
ES FR HR IT PL PT
CY LV LT LU SK FI
RO SI SE

Model: HX-03 max power: 100mA, operation: 1F
110V, 50/60Hz is attached to indoor use only.

EU product statement

The A&M Data of Europe is 2-F Mfg. Model type B00001-0-K-C has also been tested against the A&M limits. The highest A&M value capacity is 100% maximum during product evaluation. In case of the Model is 2-F Mfg. and there is no test result in 2-F Mfg. The device is not tested against the requirements of the CE mark. Therefore, the device is not CE mark. To comply compliance with RF exposure requirements, we recommend that maintain a 10cm separation distance between the user's head and the back of the handset. The user shall plug battery and another accessories during per normal mobile communication as a caution. For use of accessories that do not comply these requirements may not comply with RF exposure requirements and should be avoided.

SIZE	/	DRAWING	张迪
UNIT	mm		
SCALE	1：1	CHECKED	张冬梅

Honors /Shanghai Xiangcheng Communication Technology Co., Ltd declares that the entire equipment type [Intelligent Mobile Data Capture Terminal] is in compliance with Directive 2014/53/EU.

The full text of the EU declaration of conformity is available at the following internet address:

<http://www.xcwgtech.com/>

Cautions risk of explosion if battery is replaced by an incorrect type. Dispose of used batteries according to the instructions.

Excessive sound pressure from earphones and headphones can cause hearing loss.

SIZE	/	DRAWING	张迪	PART NO.	K7612000395LA		
UNIT	mm			TITLE	Ranger 1 K/G_movfast_快速指		
SCALE	1:1	CHECKED	张冬梅	Vender	仨睿		
SHEET	1 of 1	APPR.		DATE	2024.01.22	REV	V0.2
3rd ANGLE PROJECTION							
							