

FCC Hearing-Aid Compatibility (HAC)

1. This phone is hearing aid compatible as determined by ANSI C63.19-2019.
2. This phone has been tested and certified for use with hearing aids for some of the wireless technologies that it uses. However, there may be some newer wireless technologies used in this phone that have not been tested yet for use with hearing aids. It is important to try the different features of this phone thoroughly and in different locations, using your hearing aid or cochlear implant, to determine if you hear any interfering noise. Consult your service provider or the manufacturer of this phone for information on hearing aid compatibility. If you have questions about return or exchange policies, consult your service provider or phone retailer.
3. The ANSI C63.19-2019 standard does not use the M/T rating system for showing the hearing aid compatible of the phone that older version of the standard used, instead, the 2019 version of the standard uses the conversational gains for the phone's hearing aid compatible capabilities.
4. The volume control performance has been evaluated according to ANSI C63.19-2019 and waiver DA-23-914. The lowest conversational gain is 19.24 dB with a hearing aid, and 19.55 dB without a hearing-aid.

Codec and Air Interface combinations that have passed frequency response and distortion/noise tested.

Codec Rates (Kbps)	Air Interface
AMR-NB 12.2, AMR-WB 23.85	GSM, WCDMA, VoLTE

Codec and Air Interface combinations that have passed conversational gain tested.

Codec Rates (Kbps)	Air Interface
AMR-NB 12.2, AMR-WB 23.85	GSM, WCDMA, VoLTE
EVS-NB 24.4, EVS-WB 128	VoLTE

Codec and Air Interface combinations that have not been tested.

Codec Rates (Kbps)	Air Interface
AMR-NB 4.75-10.20, AMR-WB 6.60-23.05	GSM, WCDMA
AMR-NB 4.75-10.20, AMR-WB 6.60-23.05 EVS-NB 5.9-16.4, EVS-WB 5.9-96.0	VoLTE