

TEST SETUP PHOTOGRAPHS

Conducted Emissions Front View




Conducted Emissions Side View




Typc-C port connection adapter:

Radiated Emission 30 MHz-1 GHz View




Radiated Emission 9 kHz-30 MHz Parallel View



Radiated Emission 9 kHz-30 MHz Perpendicular View



Radiated Emission 9 kHz-30 MHz Ground-parallel View




Typc-C port connection earphone:

Radiated Emission 30 MHz-1 GHz View




Radiated Emission 9 kHz-30 MHz Parallel View



Radiated Emission 9 kHz-30 MHz Perpendicular View



Radiated Emission 9 kHz-30 MHz Ground-parallel View



Radiated Emission Above 1GHz View

