




Dieline Does Not Print

99.26 MM

Bissell® Patent Information at / Pour obtenir de l'information sur les brevets, visitez www.bissell.com/patent
 BISSSELL International Trading Company B.V.
 Postbus 1287A 1100 AW Amsterdam Zuidoost, The Netherlands
 MADE IN (SEE INDEX A)

MODEL/MOÛLE 4270 TYPE 1
 S/N: ##### (SEE INDEX B)
 14.4 V. 4800 mAh. 45 W.

ROBOTIC VACUUM CLEANER/ASPIRATEUR ROBOTIQUE
 FCC ID: 2AKK5-3208
 IC : 24578-3208
 HOUSEHOLD TYPE / TYPE MENAGER
 CONSUMER CARE / SERVICE AUX CLIENTS
 US 1-800-237-7691 CANADA 1-800-263-2535
 WWW.BISSELL.COM

WARNING - TO REDUCE THE RISK OF FIRE OR INJURY, USER MUST READ INSTRUCTION MANUAL. USE INDOORS ONLY. USE ONLY BISSELL CLEANING FLUIDS INTENDED FOR USE WITH THIS MACHINE. RISK OF INJURY FROM MOVING PARTS. BRUSH MAY START UNEXPECTEDLY. UNPLUG BEFORE CLEANING OR SERVICING.

AVERTISSEMENT - POUR RÉDUIRE LES RISQUES D'INCENDIE OU DE BLESSURE, L'UTILISATEUR DOIT LIRE LE MANUEL D'INSTRUCTIONS. UTILISER À L'INTÉRIEUR UNIQUEMENT. UTILISER UNIQUEMENT LES LIQUIDES DE NETTOYAGE BISSELL DESTINÉS À ÊTRE UTILISÉS AVEC CETTE MACHINE. RISQUE DE BLESSURE DÙ AUX PIÈCES MOBILES. LA BROUSSE PEUT DÉMARRER DE MANIÈRE INATTENDUE. DÉBRANCHER AVANT TOUT NETTOYAGE OU ENTRETIEN.

FOR ONLY USE WITH DOCKING STATION MODEL 1651031/1651034 AND BATTERY PACK MODEL 1651043/1651046. SEE INSTRUCTION MANUAL FOR ADDITIONAL DOCKING STATION AND BATTERY PACK MODEL NUMBER / À UTILISER UNIQUEMENT AVEC LA STATION D'ACCUEIL MODÈLE 1651031/1651034 ET LE BLOC-BATTERIE MODÈLE 1651043/1651046. VOIR LE MANUEL D'INSTRUCTIONS POUR LES NUMÉROS DE MODÈLE DE STATION D'ACCUEIL ET DE BATTERIE SUPPLÉMENTAIRES.

49.50 MM

80.00 MM

29.50 MM

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES. OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS :

(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE AND

(2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED, INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRED OPERATION.

1654941