


文件名称: AI MindClip-SMS-EN-2512	设计师:LBY	完成时间:2025/12/30
版本号: V1.0-2512	成品尺寸:65*85mm	
材质和工艺:80g书写纸+1专+四色、风琴折(5折) 公差:±1mm		PT2034
更改内容:更新线框图形式; 备注:不印刷此表;不印刷蓝色折页示意线		

SwitchBot AI MindClip

User Manual



Please read this user manual carefully before using your device.

Scannen Sie den QR-Code, um die deutsche Version unseres Benutzerhandbuchs zu erhalten.

Scannez le code QR pour obtenir notre manuel d'utilisation en version française.

Escanee el código QR para obtener la versión en español de nuestro manual de usuario.

Scan de QR code voor de Nederlandse versie van onze gebruikershandleiding.

Scansionate il codice QR per ottenere la versione italiana del nostro manuale d'uso.


Zeskanuj kod QR, aby pobrać instrukcję obsługi w języku polskim.

<https://www.switch-bot.com/pages/switchbot-user-manual>




User Manual

Package Contents



SwitchBot AI MindClip × 1 Type-C Charging Cable × 1

List of Components



Preparation

You will need:

- A smartphone or tablet using Bluetooth 4.2 or later.
- The latest version of our app, downloadable via the Apple App Store or Google Play Store.
- A SwitchBot account, you can register via our app or sign in to your account directly if you already have one.



iOS and Android system requirements:
<https://support.switch-bot.com/hc/en-us/articles/12567397397271>



Adding the Device

- 1 Open the SwitchBot app and sign in. Then tap the “+” icon at the top right of the home page.
- 2 Find your device's icon and select. Then follow the instructions to complete the setup.

How to Use

- Start/End recording: Use the Recording switch to control recording.
- Transfer recording to app: With Bluetooth on, open the SwitchBot app and enter AI MindClip's page. Your recording will be transferred to the app automatically.
- Transcribe recording: After a recording is transferred to your app, you can transcribe it and view a summary of it via the app.


Please note:

We continuously improve AI features through software updates. We reserve the right to the final interpretation of all functionalities. For details on data collection and usage, please visit our official website (<https://www.switch-bot.com>) and review our Privacy Policy.

How to Wear

Clip the device to your collar or the edge of your garment as shown.

Please note: For optimal recording quality, make sure the microphone is not obstructed.



Charging the Device

- Use the included Type-C charging cable to charge the device. It takes around 1.5 hours to charge the device from 20% to 100%.

- After a full battery drain:

- ① Fully charge the device.
- ② Before recording, open the SwitchBot app and connect to the device to calibrate the recording time.

LED Indicator Light

Status	Description
Solid white	Device is recording.
Light off	Recording has ended.
Slow blinking white	Transferring recording to the app.
Fast blinking white (auto-off after 120s)	Device is in pairing mode.
Fast blinking orange	Low battery.
Slow blinking orange	Device error.
Breathing orange	Device is charging.
Solid orange	Charging is completed.

Restarting the Device

Press and hold the Setup button for 15 seconds to restart the device.



Firmware Upgrades

In order to improve user experience, we will regularly release firmware updates to introduce new functions and solve any software defects that may occur during usage. When a new firmware version is available, we will send an upgrade notification to your account via our app. When upgrading, please make sure your product has sufficient battery or stay powered on and make sure your smartphone is within range to prevent interference.

FAQs

My AI MindClip can't connect to the internet.

1. Ensure your Wi-Fi is on the 2.4 GHz band.
2. Verify you've entered the correct Wi-Fi password.
3. Restart your router.
4. Restart your device.
5. If the issue persists, please contact customer support.

The LED indicator light blinks orange when I switch on/off recording.

Please add your AI MindClip to the SwitchBot app before use.

The LED indicator light is not solid white during recording.

1. Restart your device.
2. If the issue persists, please contact customer support.

Firmware upgrade failed.

1. Check your network connection.
2. Delete your device from your SwitchBot app account then re-add it.

Please note: Deleting your device will remove any recordings that have not been transferred to the app. After re-adding the device, you can find these recordings from the cloud.

How to transfer my recordings from the device to the SwitchBot app?

Your recordings will be automatically transferred to the app once you enter your AI MindClip's page in the app (make sure it is connected to the app).

- By default, your recordings are transferred via BLE.
- For a faster transfer speed, you can enable Fast Transfer via the app to directly connect your phone to the device's hotspot.

Specifications

Material: Aluminium alloy + ABS

Input: 5V $\pm$ 1A

Size: 49 × 28.5 × 19 mm (1.9 × 1.1 × 0.7 in.)

Weight: 18 g (0.6 oz.)

Operating Temperature: 0°C to 40°C (32°F to 104°F)

Connectivity: 2.4GHz Wi-Fi + Bluetooth 4.2

Warranty

We warrant to the original owner of the product that the product will be free from defects in materials and workmanship. Please note that this limited warranty does not cover:

1. Products submitted beyond the original limited warranty period.
2. Products on which repairs or modifying have been attempted.
3. Products subjected to falls, extreme temperatures, water, or other operating conditions outside the product specifications.
4. Damage due to natural disaster (including but not limited to lightning, flood, tornado, earthquake, or hurricane, etc.).
5. Damage due to misuse, abuse, negligence or casualty (e.g. fire).
6. Other damage that is not attributable to defects in the manufacture of product materials.
7. Products purchased from unauthorized resellers.
8. Consumable parts (including but not limited to batteries).
9. Natural wear of the product.

Contact & Support

Feedback: If you have any concerns or problems when using our products, please send feedback via our app through the Profile > Support page.

Setup and Troubleshooting: support.switch-bot.com

Support Email: support@switch-bot.com

文件名称:AI MindClip-合规声明-7in1-2512	设计师:ZBH	完成时间: 2025/12/23
版本号:V1.0-AI MindClip-HGSM-7in1-2512		尺寸:45*60mm
材质工艺: 80g书写纸+印黑色 (K=90) +风琴折		
更改内容: 备 注:蓝色线框为折页线, 不印刷; 本表格不印刷。		

SwitchBot Regulatory Compliance Information

CE Warning

For the countries that adopt the SAR limit of 2.0 W/kg(Body) and 4.0 W/kg(Limbs) over 10 grams of tissue. The device complies with RF specifications when used at a distance of 0.0 cm from your Body/Limbs.

CE DOC

Hereby, Woan Technology (Shenzhen) Co., Ltd. declares that the radio equipment type is in compliance with Directive 2014/53/EU. The full text of the EU declaration of conformity is available at the following internet address: support.switch-bot.com

This product can be used in EU member states and UK.

Manufacturer: Woan Technology (Shenzhen) Co., Ltd.
Address: Room 1101, Qiancheng Commercial Center, No. 5 Haicheng Road, Mabu Community, Xixiang Subdistrict, Bao'an District, Shenzhen, Guangdong, P.R.China, 518100

E-mail: support@switch-bot.com

CE representative: XDH Tech

Address: 2 Rue Coysevox Bureau 3, Lyon, France

E-mail: xdh.tech@outlook.com

Operation frequency (Max power)

2.4GHz Wi-Fi:

Frequency band(s): 2412-2472 MHz

Maximum RF power transmitted: <20dBm (e.i.r.p.)

2.4GHz Bluetooth:

Frequency band(s): 2402-2480 MHz

Maximum RF power transmitted: <10dBm (e.i.r.p.)

Operation temperature: 0 to 40 °C

FCC Warning

This device complies with Part 15 of the FCC Rules.

Operation is subject to the following two conditions:

(1) This device may not cause harmful interference.

(2) This device must accept any interference received, including interference that may cause undesired operation.

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation.

This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.

- Increase the separation between the equipment and receiver.

- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

- Consult the dealer or an experienced radio/TV technician for help.

NOTE: The manufacturer is not responsible for any radio or TV interference caused by unauthorized modifications

to this equipment. Such modifications could void the user's authority to operate the equipment.

The SAR limit of FCC is 1.6 W/kg averaged over one gram of tissue. Device has also been tested against this SAR limit. The testing distance of body is 0mm.

CE-Warnung

Für Länder, die den SAR-Grenzwert von 2,0 W/kg (Körperstamm) und 4,0 W/kg (Gliedermaßen) bezogen auf 10 Gramm Gewebe anwenden. Das Gerät entspricht den HF-Spezifikationen, wenn es mit einem Abstand von 0,0 cm zu Ihrem Körper/Ihren Gliedmaßen verwendet wird.

CE-DOC

Hiermit erklärt Woan Technology (Shenzhen) Co., Ltd. dass die Funkanlage mit der Richtlinie 2014/53/EU übereinstimmt. Der vollständige Text der EU-Konformitätserklärung ist unter der folgenden Internetadresse verfügbar: support.switch-bot.com
Dieses Produkt kann in den EU-Mitgliedsstaaten und in Großbritannien verwendet werden.

Hersteller: Woan Technology (Shenzhen) Co., Ltd.

Adresse: Raum 1101, Qiancheng Commercial Center, Nr. 5 Haicheng Road, Mabu Community, Xixiang Subdistrict, Bao'an District, Shenzhen, Guangdong, P.R.China, 518100

E-mail: support@switch-bot.com

CE-Vertreter: XDH Tech

Anschrift: 2 Rue Coysevox Bureau 3, Lyon, Frankreich

E-mail: xdh.tech@outlook.com

Betriebsfrequenz (Maximale Leistung)

2,4 GHz Wi-Fi:

Frequenzband: 2412-2472 MHz

Maximale übertragene HF-Leistung: <20 dBm (e.i.r.p.)

2,4 GHz Bluetooth:

Frequenzband: 2402-2480 MHz

Maximale übertragene HF-Leistung: <10 dBm (e.i.r.p.)

Betriebstemperatur: 0 °C bis 40 °C

Avertissement CE

Pour les pays qui adoptent la limite DAS de 2,0 W/kg (corps) et 4,0 W/kg (membres) pour 10 grammes de tissu. L'appareil est conforme aux spécifications RF lorsqu'il est utilisé à une distance de 0,0 cm de votre corps/membres.

CE DOC

Par la présente, Woan Technology (Shenzhen) Co, Ltd déclare que le type d'équipement radio est conforme à la directive 2014/53/UE. Le texte intégral de la déclaration de conformité UE est disponible à l'adresse internet suivante : support.switch-bot.com.

Ce produit peut être utilisé dans les États membres de l'UE et au Royaume-Uni.

Fabricant : Woan Technology (Shenzhen) Co, Ltd.

Adresse : Appartement 1101, Centre Commercial de Qiancheng, No. 5 de la route de Haicheng, Communauté de Mabu, Sub-district de Xixiang, District de Bao'an, Shenzhen, Guangdong, République populaire de Chine, 518100

E-mail: support@switch-bot.com

Représentant CE : XDH Tech

Adresse : 2 Rue Coysevox Bureau 3, Lyon, France

E-mail: xdh.tech@outlook.com

Fréquence de fonctionnement (Puissance maximale)

Wi-Fi 2,4 GHz:

Plage de fréquences: 2412-2472 MHz

Puissance RF maximale transmise: <20 dBm (e.i.r.p.)

Bluetooth 2,4 GHz:

Plage de fréquences: 2402-2480 MHz

Puissance RF maximale transmise: <10 dBm (e.i.r.p.)

Température de fonctionnement : 0 à 40 °C

Avvertenza di CE

Per i paesi che adottano il limite SAR di 2,0 W/kg (corpo) e 4,0 W/kg (arti) su 10 grammi di tessuto. Il dispositivo è conforme alle specifiche RF se utilizzato a una distanza di 0,0 cm dal corpo/arti.

DOC CE

Con la presente, Woan Technology (Shenzhen) Co., Ltd. dichiara che il tipo di apparecchiatura radio è conforme alla Direttiva 2014/53/UE. Il testo completo della dichiarazione di conformità UE è disponibile al seguente indirizzo internet: support.switch-bot.com

Questo prodotto può essere utilizzato negli Stati membri dell'UE e nel Regno Unito.

Produttore: Woan Technology (Shenzhen) Co., Ltd.

Indirizzo: Room 1101, Qiancheng Commercial Center, No. 5 Haicheng Road, Mabu Community, Xixiang Subdistrict, Bao'an District, Shenzhen, Guangdong, P.R.China, 518100

E-mail: support@switch-bot.com

Rappresentante CE: XDH Tech

Indirizzo: 2 Rue Coysevox Bureau 3, Lione, Francia

E-mail: xdh.tech@outlook.com

Frequenza di funzionamento (Potenza massima)

Wi-Fi 2,4 GHz:

Bande di frequenza: 2412-2472 MHz

Potenza RF massima trasmessa: <20 dBm (e.i.r.p.)

Bluetooth 2,4 GHz:

Bande di frequenza: 2402-2480 MHz

Potenza RF massima trasmessa: <10 dBm (e.i.r.p.)
Temperatura di funzionamento: Da 0 a 40 °C

Advertencia CE

Para los países que adoptan el límite de SAR de 2,0 W/kg (cuerpo) y 4,0 W/kg (extremidades) sobre 10 gramos de tejido. El dispositivo cumple con las especificaciones de RF cuando se usa a una distancia de 0,0 cm del cuerpo/ extremidades.

DOC CE

Por la presente, Woan Technology (Shenzhen) Co., Ltd. declara que el equipo de radio cumple con la Directiva 2014/53/UE. El texto completo de la declaración de conformidad de la UE está disponible en la siguiente dirección de internet: support.switch-bot.com

Este producto puede ser utilizado en los estados miembros de la UE y el Reino Unido.

Fabricante: Woan Technology (Shenzhen) Co., Ltd.

Dirección: Sala 1101, Centro Comercial Qiancheng, No. 5 Haicheng Road, Comunidad Mabu, Subdistrito Xixiang, Distrito Bao'an, Shenzhen, Guangdong, P.R.China, 518100

E-mail: support@switch-bot.com

Representante CE: XDH Tech

Dirección: 2 Rue Coysevox Bureau 3, Lyon, Francia

E-mail: xdh.tech@outlook.com

Frecuencia de Operación (Potencia máxima)

Wi-Fi de 2,4 GHz:

Banda de frecuencias: 2412–2472 MHz

Potencia máxima de RF transmitida: <20 dBm (e.i.r.p.)

Bluetooth de 2,4 GHz:

Banda de frecuencias: 2402–2480 MHz

Potencia máxima de RF transmitida: <10 dBm (e.i.r.p.)

Temperatura de operación: 0 a 40 °C

CE Waarschuwing

Voor landen die de SAR-limiet hanteren van 2,0 W/kg (lichaam) en 4,0 W/kg (ledematen) over 10 gram weefsel. Het apparaat voldoet aan de RF-specificaties wanneer het op een afstand van 0,0 cm van uw lichaam/ledematen wordt gebruikt.

CE DOC

Hierbij verklaart Woan Technology (Shenzhen) Co., Ltd. dat de radiouitrusting van het type voldoet aan Richtlijn 2014/53/EU. De volledige tekst van de EU-verklaring van conformiteit is beschikbaar op het volgende internetadres: support.switch-bot.com

Dit product kan worden gebruikt in EU-lidstaten en het Verenigd Koninkrijk.

Fabrikant: Woan Technology (Shenzhen) Co., Ltd.

Adres: Kamer 1101, Qiancheng Commercial Center, Nr. 5 Haicheng Road, Mabu Community, Xixiang Subdistrict, Bao'an District, Shenzhen, Guangdong, V.R. China, 518100

E-mail: support@switch-bot.com

CE-vertegenwoordiger: XDH Tech

Adres: 2 Rue Coysevox Bureau 3, Lyon, Frankrijk

E-mail: xdh.tech@outlook.com

Werkfrequentie (Maximale vermogen)

2,4 GHz Wi-Fi:

Frequentieband(en): 2412–2472 MHz

Maximaal verzonden RF-vermogen: <20 dBm (e.i.r.p.)

2,4 GHz Bluetooth:

Frequentieband(en): 2402–2480 MHz

Maximaal verzonden RF-vermogen: <10 dBm (e.i.r.p.)

Bedrijfstemperatuur: 0 tot 40 °C

Ostrzeżenie CE

Dla krajów, które przyjmują limit SAR wynoszący 2,0 W/kg (tułów) i 4,0 W/kg (kończyny) na 10 gramów tkanki. Urządzenie jest zgodne ze specyfikacjami RF, gdy jest używane w odległości 0,0 cm od ciała/kończyn.

CE DOC

Niniejszym firma Woan Technology (Shenzhen) Co., Ltd. oświadcza, że typ urządzenia radiowego jest zgodny z dyrektywą 2014/53/UE. Pełny tekst deklaracji zgodności UE jest dostępny pod następującym adresem internetowym: support.switch-bot.com

Ten produkt może być używany w państwach członkowskich UE i Wielkiej Brytanii.

Producent: Woan Technology (Shenzhen) Co., Ltd.

Adres: Room 1101, Qiancheng Commercial Center, No. 5 Haicheng Road, Mabu Community, Xixiang Subdistrict, Bao'an District, Shenzhen, Guangdong, U.R. China, 518100

E-mail: support@switch-bot.com

Przedstawiciel CE: XDH Tech

Adres: 2 Rue Coysevox Office 3, Lyon, Francja

E-mail: xdh.tech@outlook.com

Częstotliwość pracy (moc maksymalna).

Wi-Fi 2,4 GHz:

Pasmo(a) częstotliwości: 2412-2472 MHz

Maksymalna transmitowana moc RF: <20 dBm (e.i.r.p.)

Bluetooth 2,4 GHz:

Pasmo(a) częstotliwości: 2402-2480 MHz

Maksymalna transmitowana moc RF: <10 dBm (e.i.r.p.)

Temperatura pracy: 0 do 40 °C