


NR2_30 M_Band Edge_Low_BPSK_1RB



NR2_30 M_Band Edge_Low_BPSK_FullRB



NR2_30 M_Extended Band Edge_Low_BPSK_FullRB




NR2_30 M_Band Edge_High_BPSK_1RB



NR2_30 M_Band Edge_High_BPSK_FullRB



NR2_30 M_Extended Band Edge_High_BPSK_FullRB




NR2_40 M_Band Edge_Low_BPSK_1RB



NR2_40 M_Band Edge_Low_BPSK_FullRB



NR2_40 M_Extended Band Edge_Low_BPSK_FullRB




NR2_40 M_Band Edge_High_BPSK_1RB



NR2_40 M_Band Edge_High_BPSK_FullRB



NR2_40 M_Extended Band Edge_High_BPSK_FullRB



12. ANNEX A_ TEST SETUP PHOTO

Please refer to test setup photo file no. as follows;

No.	Description
1	HCT-RF-2510-FC019-P