



NR66_25 M_Band Edge_High_BPSK_FullRB



NR66_25 M_Extended Band Edge_High_BPSK_FullRB




NR66_30 M_Band Edge_Low_BPSK_1RB




NR66_30 M_Band Edge_Low_BPSK_FullRB



NR66_30 M_Extended Band Edge_Low_BPSK_FullRB




NR66_30 M_Band Edge_High_BPSK_1RB



NR66_30 M_Band Edge_High_BPSK_FullRB



NR66_30 M_Extended Band Edge_High_BPSK_FullRB




NR66_40 M_Band Edge_Low_BPSK_1RB




NR66_40 M_Band Edge_Low_BPSK_FullRB



NR66_40 M_Extended Band Edge_Low_BPSK_FullRB




NR66_40 M_Band Edge_High_BPSK_1RB



NR66_40 M_Band Edge_High_BPSK_FullRB





12. ANNEX A_ TEST SETUP PHOTO

Please refer to test setup photo file no. as follows;

No.	Description
1	HCT-RF-2501-FC048-P