


DUT and SAR Set-up Photos

Photograph 1: Overall Dimensions



Photograph 2: Front View of the DUT




Photograph 3: Rear View of the DUT



Setup Photos

Photograph 4: Vertical and Horizontal Reference Lines

Vertical
Center Line




Horizontal
Line

Body-worn Accessory & Hotspot mode Exposure Conditions

Photograph 5: Body & Hotspot, Back, 0 mm, Front View




Photograph 6: Body & Hotspot, Back, 0 mm, Side View



Photograph 7: Body & Hotspot, Back, 18 mm, Front View




Photograph 8: Body & Hotspot, Back, 18 mm, Side View



Photograph 9: Body & Hotspot, Edge Top, 0 mm, Front View




Photograph 10: Body & Hotspot, Edge Top, 0 mm, Side View



Photograph 11: Body & Hotspot, Edge Top, 22 mm, Front View




Photograph 12: Body & Hotspot, Edge Top, 22 mm, Side View



Photograph 13: Body & Hotspot, Edge Top, 25 mm, Front View




Photograph 14: Body & Hotspot, Edge Top, 25 mm, Side View



Photograph 15: Body & Hotspot, Edge Right, 0 mm, Front View




Photograph 16: Body & Hotspot, Edge Right, 0 mm, Side View




Photograph 17: Body & Hotspot, Edge Right, 11 mm, Front View




Photograph 18: Body & Hotspot, Edge Right, 11 mm, Side View




Photograph 19: Body & Hotspot, Edge Left, 0 mm, Front View




Photograph 20: Body & Hotspot, Edge Left, 0 mm, Side View



Photograph 21: Body & Hotspot, Edge Left, 10 mm, Front View



Photograph 22: Body & Hotspot, Edge Left, 10 mm, Side View



Antenna Dimensions & Separation Distances

