

APPENDIX 3: Photographs of test setup

Conducted emission (1/2)

Serial No.: 9000001



UL Japan, Inc.

Shonan EMC Lab.



1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken 259-1220 JAPAN

Telephone: +81 463 50 6400

Facsimile: +81 463 50 6401

Conducted emission (2/2)

Serial No.: 9000002



UL Japan, Inc.
Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken 259-1220 JAPAN

Telephone: +81 463 50 6400

Facsimile: +81 463 50 6401

Radiated emission (1/2)

Serial No.: 9000001

Front



Rear

9 kHz - 30 MHz



30 MHz - 1000 MHz



1 GHz - 10 GHz



UL Japan, Inc.
Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken 259-1220 JAPAN

Telephone: +81 463 50 6400

Facsimile: +81 463 50 6401

Radiated emission (2/2)

Serial No.: 9000002

Front



Rear

9 kHz - 30 MHz



30 MHz - 1000 MHz



1 GHz - 10 GHz



END OF REPORT

UL Japan, Inc.
Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken 259-1220 JAPAN

Telephone: +81 463 50 6400

Facsimile: +81 463 50 6401