

EXHIBIT 1

Label Drawing

Label Drawing

Please refer **Exhibit 2 Figure 2 (Page 10)** for Label Placement Location

LOCATED ON REAR ENCLOSURE

AOC COLOR MONITOR Model No: 5Vlr Power Rating: 100-240V~50/60Hz 1.5A AOC International 311 Sinclair Frontage Road Milpitas, CA 95035 USA Geprüft nach Tested Acc. to MPR II: MPR 1990.8/1990.10 Made in China 40A155-073	FCC ID: ARSCM569N This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus meets all requirements of the Canadian Interference - Causing Equipment Regulations. Cet appareil numérique de la classe B respecte toutes les exigences du Règlement sur le matériel brouilleur du Canada. THIS DEVICE COMPLIES WITH FDA RADIATION PERFORMANCE STANDARDS, 21 CFR SUBCHAPTER J. Die in diesem Gerät entstehende Röntgenstrahlung ist ausreichend abgeschirmt. Beschleunigungsspannung: max. 25KV Cathode Ray Tube intrinsically safe according to appendix II Röntgenverordnung Eigensichere Kathodenstrahlröhre nach Anlage II Röntgenverordnung
 E135889 LISTED L.T.E. MONITOR 1001  LF950441	   ENERGY STAR EPA FILIATION PROGRAM

Figure 2
General Appearance (Rear View)

