

Test Set-Up Photos

1. Conducted Emission Test



FRONT VIEW



BACK VIEW

2. Radiated Electromagnetic Emission Test




FRONT VIEW OF RADIATED EMISSION TEST



BACK VIEW OF RADIATED EMISSION TEST



*SETUP WITH MAXIMUM DETECTED EMISSION AT HORIZONTAL POLARIZATION
(TEST MODE: D-SUB 1024*768@60Hz, ADAPTER: ADS-24NP-12-1 12024G)*



*SETUP WITH MAXIMUM DETECTED EMISSION AT VERTICAL POLARIZATION
(TEST MODE: D-SUB 1024*768@60Hz, ADAPTER: ADS-24NP-12-1 12024G)*