
APPENDIX 3: Photographs of test setup

Conducted emission



(Front)



(Side)

UL Japan, Inc.


Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken, 259-1220 JAPAN

Telephone : +81 463 50 6400

Facsimile : +81 463 50 6401

Radiated emission




(Front)



(Rear ,Horizontal, below 30 MHz)



(Rear ,Vertical, below 30 MHz)



(Rear, above 30 MHz)

UL Japan, Inc.

Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken, 259-1220 JAPAN

Telephone : +81 463 50 6400


Facsimile : +81 463 50 6401

Pre-check of the worst position

Without - tag
X-axis



With - tag
X-axis



Y-axis



Y-axis



Z-axis



Z-axis



UL Japan, Inc.

Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken, 259-1220 JAPAN

Telephone : +81 463 50 6400

Facsimile : +81 463 50 6401

Tag appearance

Type A




Front




Rear

Type B




Front



Rear

Type F



Front



Rear

END OF REPORT

UL Japan, Inc.

Shonan EMC Lab.

1-22-3 Megumigaoka, Hiratsuka-shi, Kanagawa-ken, 259-1220 JAPAN

Telephone : +81 463 50 6400

Facsimile : +81 463 50 6401