



**CDMA Mask Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGVL-2061XXSYS.**

Test Set-up



Conducted Emission Limits Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGVL-2061XXSYS.

Test Set-up




TEST SETUP FOR RADIATED EMISSIONS TESTING


OAKWOOD LAB

Notes:

1. Items shown in dotted lines are located on the floor below the test area. It is 5 meters vertically from the ground floor to test area.
2. 50 Hz and 60 Hz are power panels for alternating current.
3. The antenna may be positioned horizontally 3 or 10 meters from the center of the turntable.
4. The circle is a 6.7 meter diameter turntable.
5. A ground plane is in the plane of this sheet.
6. The test sample is shown in the azimuthal position representing zero degrees.



Radiated Emissions Test Setup:




Radiated Emissions Test Setup:




Effective Isotropic Radiated Power Limit Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGPL-2061XXSYS.

Test Set-up




**Frequency Tolerance Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGVL-2061XXSYS.**

EUT Host is specified for indoor use only with temperature range of 0° to +50° C, and was tested with its range.
EUT STM and LPA are specified with a temperature range of -30° to +50° C and were tested with their range.



**Inter-Modulation Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGVL-2061XXSYS.**



Occupied Bandwidth Modulation Test for ADC Inc.
Digivance SMR 20 Watt System
Model Number DGPL-2061XXSYS.

Test Set-up

