


DOCUMENT CLASSIFICATION	TITLE	DOCUMENT No.
Qualification Test Report	Mechanical testing and environmental testing of I-PEX MHF and HIROSE U.FL connector	TR-1029

(7) Thermal shock


Contact resistance of inner contact

Plug Receptacle	Initial			
	I-PEX	I-PEX	HIROSE	HIROSE
AVE.	1.20	1.20	1.20	1.20
MAX.	1.8	1.8	1.8	1.8
MIN.	0.9	0.9	0.9	0.9
S	0.28			
Plug Receptacle	After testing			
	I-PEX	I-PEX	HIROSE	HIROSE
AVE.	1.32	1.62	1.72	1.88
MAX.	1.9	1.9	2.6	3.0
MIN.	0.9	1.2	1.2	1.3
S	0.32			
Units	mille-ohm	mille-ohm	mille-ohm	mille-ohm
Sample quantity	10pcs.	5pcs.	5pcs.	5pcs.



Contact resistance of ground contact

Plug Receptacle	Initial			
	I-PEX	I-PEX	HIROSE	HIROSE
AVE.	1.22	1.08	1.44	1.28
MAX.	1.8	1.4	1.7	1.6
MIN.	0.9	0.8	1.1	1.1
S	0.35			
Plug Receptacle	After testing			
	I-PEX	I-PEX	HIROSE	HIROSE
AVE.	1.29	1.24	1.56	1.42
MAX.	2.0	1.5	1.9	1.7
MIN.	0.9	1.0	1.1	1.2
S	0.37			
Units	mille-ohm	mille-ohm	mille-ohm	mille-ohm
Sample quantity	10pcs.	5pcs.	5pcs.	5pcs.




DOCUMENT CLASSIFICATION	TITLE	DOCUMENT No.
Qualification Test Report	Mechanical testing and environmental testing of I-PEX MHF and HIROSE U.FL connector	TR-1029

(8) Humidity


Contact resistance of inner contact

	Initial			
Plug	I-PEX	I-PEX	HIROSE	HIROSE
Receptacle	I-PEX	HIROSE	I-PEX	HIROSE
AVE.	1.51	1.60	1.84	1.46
MAX.	2.1	2.1	2.6	2.1
MIN.	0.8	1.1	0.8	1.2
S	0.41			
	After testing			
Plug	I-PEX	I-PEX	HIROSE	HIROSE
Receptacle	I-PEX	HIROSE	I-PEX	HIROSE
AVE.	1.66	1.74	1.96	1.56
MAX.	2.1	2.2	2.9	2.4
MIN.	1.1	1.3	0.9	1.2
S	0.34			
Units	mille-ohm	mille-ohm	mille-ohm	mille-ohm
Sample quantity	10pcs.	5pcs.	5pcs.	5pcs.




Contact resistance of ground contact

	Initial			
Plug	I-PEX	I-PEX	HIROSE	HIROSE
Receptacle	I-PEX	HIROSE	I-PEX	HIROSE
AVE.	1.44	1.52	1.20	1.96
MAX.	1.8	1.7	1.7	2.8
MIN.	1.0	1.3	0.8	0.7
S	0.25			
	After testing			
Plug	I-PEX	I-PEX	HIROSE	HIROSE
Receptacle	I-PEX	HIROSE	I-PEX	HIROSE
AVE.	1.55	1.66	1.30	2.06
MAX.	1.9	2.0	1.8	2.9
MIN.	1.2	1.4	0.9	1.0
S	0.25			
Units	mille-ohm	mille-ohm	mille-ohm	mille-ohm
Sample quantity	10pcs.	5pcs.	5pcs.	5pcs.



Patent of MHF series micro coaxial connector

No. IER-001-00572



					Prepared by	Reviewed by	Approved by
1	R1111	K.O	AUG/30/01	<i>K.O.</i>	K.Ohbayashi JUL / 05 / 01	E.Kawabe JUL / 06 / 01	K.Katabuchi JUL / 09 / 01
0	R1063	K.O	JUL/05/01	<i>K.O.</i>			
REV.	ECN	BY	DATE	APP.			
REVISION RECORD							

DOCUMENT CLASSIFICATION	TITLE	No.
Technical Report	Patent of MHF series micro coaxial connector	IER-001-00572
1. Name, part No. :MHF series micro coaxial connector , 20278-001R-**,20279-001E-01 2. Contents Our MHF series micro coaxial connector does not conflict with Hirose's patent under our research of patent issues at this moment. 弊社MHFシリーズ超小型同軸コネクタは、弊社調査結果においてはヒロセ電機の特許に抵触していない事を報告します。		

 SUMITOMO ELECTRIC INDUSTRIES, LTD

Sheet No. _____1_____

3-3, Satsuki-cho, Kanuma, Tochigi, 322-8585 JAPAN
Tel.(028978)-0324 Fax.(028976)-2789

Head Office : Osaka
International Div: Tokyo

Messrs, _____High Tek_____

Date _____Oct. 9, 2002_____
Spec. No, _____IEE8-01026B_____


SPECIFICATION

FOR

LVCX Series
50Ω SUMIFRON® Insulation Coaxial Cable

0.7DS-PBE (COLOR)

SIGNED BY _____



K. Yokoi

Manager of Data Transmission
Engineering Section
Data Transmission Cable
Component Department
Electronic Wire Division