

8

7

6

5

4

3

2

1


REVISIONS				
ECN #	REV.	DESCRIPTION	DATE	APPROVED
	A	PRODUCTION RELEASE	10/1/03	TM
361	B	FCC ID# WAS JIAXTM1	11/5/03	TM

3.00

DO NOT OPEN
UNTIL READY FOR USE

MAKE
"ACTIVATE SENSOR"
TEXT BOLD

ACTIVATE Capsule before swallowing
1. Align lens end of Capsule with
Activation Port on right side of Monitor.
2. Press Activate Sensor key on front
of Monitor while holding lens end of
Capsule in Activation Port.
3. Follow prompts on Monitor display.
4. If activation fails, try to activate again
after 5 seconds, by repeating the first 3
steps above.
5. When activation is successful, swallow
Capsule with water.
CAUTION: DO NOT CHEW CAPSULE!
DO NOT INGEST CAPSULE IF
VISIBLY DAMAGED!



5.10

FRONT

DO NOT OPEN
UNTIL READY FOR USE

How Supplied: 1 Capsule per package.

Single-use Capsule.

Reception Range: 1 meter

Operating Time: 240 hours

Mini Mitter Company, Inc.
20300 Empire Ave., Bldg. B-3
Bend, OR 97701 USA
541-322-7272
www.minimitter.com

FCC ID#: JIAXTP1

SERIAL #

EXPIRATION DATE

BACK

NOTES U.O.S.:
MATERIAL DESIGNATION: 48 ga PET / 98 ga WOPP / .00030 Foil / 1.75 mil PE
FILM SPECIFICATIONS:
48 ga PET, .00048 In., 10.36 lb / ream, +/- 10% Adhesive .0001 In., 1.71 lb / ream, -10% + 25%
98 ga White OPP, .00098 In., 14.74 lb / ream, +/- 10% Adhesive .0001 In., 1.7 lb / ream, -10% + 25%
Aluminum Foil, .00030 In., 12.63 lb / ream,, +/- 10% Adhesive .0001 In., 1.7 lb / ream, -10% + 25%
Peelable Film, .00175 In., 25.2 lb / ream +/- 10% Typical Values: 3.81, 68.14 lb / ream, +/- 10%
Yeild: 6,350 square inches per pound +/- 10%
MOISTURE BARRIER: MVTR = TYPICAL .006 / 100 sq. Inches / 24 Hours / 90 TO 100% R.H. / 100 Degrees F
OXYGEN TRANSMISSION: < 0.01 cc / 100 sq. Inches / 24 Hours / 75 Degrees F / 75% R.H.
PRINTING:
FONT: NEW TIMES ROMAN, 10 PT; (MAIN BODY OF TEXT)
CENTURY GOTHIC, 13 PT; (DO NOT OPEN WARNING)
COLOR: BLACK

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MINI MITTER CO., INC. AND REPRESENTS A PROPRIETARY ARTICLE IN WHICH MINI MITTER RETAINS ANY AND ALL PATENT RIGHTS, INCLUDING EXCLUSIVE RIGHTS OF USE AND/OR MANUFACTURE, AND/OR SALE. POSSESSION OF THIS PRINT DOES NOT CONVEY ANY PERMISSION TO REPRODUCE PRINT OR MANUFACTURE ARTICLE(S) SHOWN HEREIN. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MINI MITTER IS PROHIBITED. SPECIFICATION CANNOT BE CHANGED WITHOUT THE APPROVAL OF MINI MITTER.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
TWO PLACE DECIMAL ± 0.050"
ONE PLACE DECIMAL ± 0.100"
ANGULAR: MACH± 0.5 DEG
BEND: ±



MINI MITTER CO., INC,
20300 Empire Avenue, Bldg. B-3
Bend, OR 97701

	NAME	DATE	TITLE: PACKAGING ENVELOPE, INNER, CAPSULE SENSOR		
DRAWN	Tom Meyer	3/20/03			
CHECKED					
ENG APPR.	Florian Bell	Engineering Release	SIZE B	DWG. NO. 018-0252-00	REV B
COMMENTS: DO NOT SCALE DRAWING			SCALE: 1:1	USED ON VitalSense	SHEET 1 OF 1