

ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS
Siemens Milltronics SITRANS LR

PHOTO # 1



ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS
Siemens Milltronics SITRANS LR

PHOTO # 2



ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS

Siemens Milltronics SITRANS LR

PHOTO # 3

Carrier and spurious/harmonic emissions from the Siemens Milltronics SITRANS LR, which was mounted on top of the metal tank without ventilation, were scanned using a horn antenna at 0.5, 1.0 and 3 meters distances.

Metal tank



ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS
Siemens Milltronics SITRANS LR

PHOTO # 4

Concrete cement tank contains cement



ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS
Siemens Milltronics SITRANS LR

PHOTO # 5

The Siemens Milltronics SITRANS LR mounted on top of the mouth of the Concrete Tank



ANNEX 2 - PHOTOGRAPHS OF RADIATED EMISSIONS MEASUREMENTS

Siemens Milltronics SITRANS LR

PHOTO # 6

Carrier and spurious/harmonic emissions from the Siemens Milltronics SITRANS LR , which was mounted on top of the concrete tank, were scanned using a horn antenna at 0.5, 1.0 and 3 meters distances.

