




Appendix D

Photographs

1. SAR measurement System
2. Photographs of Tissue Simulate Liquid
3. Photographs of EUT test position
4. EUT Constructional Details

1. SAR measurement System



2. Photographs of Tissue Simulate Liquid













Photo 1: Tissue Simulant Liquid for Head 750	Photo 2: Tissue Simulant Liquid for Body 750
	
Photo 3: Tissue Simulant Liquid for Head 835	Photo 4: Tissue Simulant Liquid for Body 835
	
Photo 5: Tissue Simulant Liquid for Head 1750	Photo 6: Tissue Simulant Liquid for Body 1750
	

Photo 7: Tissue Simulant Liquid for Head 1900	Photo 8: Tissue Simulant Liquid for Body 1900
	
Photo 9: Tissue Simulant Liquid for Head 2450	Photo 10: Tissue Simulant Liquid for Body 2450
	
Photo 11: Tissue Simulant Liquid for Head 2600	Photo 12: Tissue Simulant Liquid for Body 2600
	

3. Photographs of EUT test position






Photo 13: Left touch cheek	Photo 14: Left tilted 15 degree
	
Photo 15: Right touch cheek	Photo 16: Right tilted 15 degree
	
Photo 17: Front side 15mm	Photo 18: Back side 15mm
	

Photo 19: Front side 10mm	Photo 20: Back side 10mm
	
Photo 21: Left side 10mm	Photo 22: Right side 10mm
	
Photo 23: Top side 10mm	Photo 24: Bottom side 10mm
	

4. EUT Constructional Details

Photo 25: Front View	Photo 26: Back View
 A black smartphone is shown from the front, lying on a blue textured surface. A white ruler is placed vertically to the left of the phone, and another white ruler is placed horizontally below the phone. The phone's screen is dark, and the front-facing camera and sensors are visible at the top. The bottom of the phone shows three capacitive touch buttons.	 A black smartphone is shown from the back, lying on a blue textured surface. A white ruler is placed vertically to the left of the phone, and another white ruler is placed horizontally below the phone. The back of the phone features a camera lens, a flash, and the 'UMAX' brand name. A small logo is visible at the bottom center.