

Variant description in relation to FCC rules § 2.1031

This document describes the difference between **KIRK handset 4040 2.4 GHz** (PP5N 2G4) and **KIRK handset 4020 2.4 GHz** (PP5N20 2G4).

In order to create a low cost variant the vibrator and audio-jack is omitted in the 4020 version of the handset. A “dummy jack”- plastic brick is used to close the hole for the audio-jack and the name and color on the front-plate is changed. Two 0 ohm resistors are mounted instead of the audio-jack in order to bypass the audio signal. The following list shows the parts mentioned above.

8467 1110	JACK Ø2.5MM FEMALE
8422 9797	JUMPER 0R 0603
8466 7408	MOTOR VIBRATOR 1.3VDC SPRING
1409 5601	LENS, IMF, PP5 (front plate)
1409 5100	DUMMY JACK