



Appendix D. Photo documentation

Table of contents
Test Facility
Test Positions
Liquid depth

Test Facility

Photo 1: Measurement System DASY5



Test Positions

Photo 2: Front View



Photo 3: Back View



Photo 4: Left hand touch cheek



Photo 5: Left hand tilt 15°



Photo 6: Right hand touch cheek



Photo 7: Right hand tilt 15°



Photo 8: Front Side (15mm)



Photo 9: Back Side (15mm)



Photo 10: Front Side (10mm)



Photo 11: Back Side (10mm)



Photo 12: Left Side (10mm)



Photo 13: Right Side (10mm)



Photo 14: Top Side (10mm)



Photo 15: Bottom Side (10mm)



Photo 16: Back Side (0mm)



Photo 17: Bottom Side (0mm)



Liquid depth

Photo 18: HSL 835MHz depth (15.2cm)



Photo 19:MSL 835MHz depth (15.1cm)




Photo 20:HSL 1750MHz depth (15.3cm)



Photo 21:MSL 1750MHz depth (15.1cm)




Photo 22:HSL 1900MHz depth (15.3cm)



Photo 23:MSL 1900MHz depth (15.1cm)




Photo 24:HSL 2450MHz depth (15.1cm)



Photo 25:MSL 2450MHz depth (15.2cm)




Photo 26:HSL 2600MHz depth (15.2cm)



Photo 27:MSL 2600MHz depth (15.3cm)

