
* Introduction

No wires. No limits. Enjoy the convenience of hands-free communication with total freedom of movement.

DOnetworks' DOFree Bluetooth headset, very comfortable when it's worn, easy to use, is a high-tech wireless hands-free product.

Automatically link to other Bluetooth technology enabled products up to 10 meters(33 ft) away without ever touching the devices. Store in a pocket, in a briefcase, across the room or even in the trunk of a car and enjoy effortless, quality communication. All calls are transmitted wirelessly to your earpiece. DOFree gives you easy, intuitive access to volume controls, features LED and audible status indicators.

Much work has gone into making the DOFree as practical and easy to use as possible. The ear loop is flexible enough to fit most ears and sturdy enough to hold the headset firmly in place. The user can put it on with one hand and move around freely just pressing a button on the control unit to answer or reject calls.

The DOFree is the ideal accessory for people who lead an active life.

DOnetworks' DOFree Bluetooth headset will be the key to the people who use cell-phone excessively while driving, sporting, travel, etc.

* Features

The smallest size, ultra lightweight

DOFree is ultra lightweight; extremely portable, comfortable to wear for a long phone call. DOFree is easy to quickly and conveniently put the headset on your ear, and to take off again and easy to use the control buttons on the headset.

Free Your Hands - Free Your Life

Invest in increased efficiency, greater freedom of movement, and a major upgrade in mobile style with the DOnetworks. This compact headset is equipped with a wireless connection, giving you hands-free control over your mobile phone without the need for obtrusive cables or wires. Designed for both looks and comfort, the DOFree fits inconspicuously in either ear, allowing you convenient and discreet access to all basic call controls-whether your phone is stashed away in your briefcase or lying on a table nearby.

The high quality of your conversation

The DOFree headset, the latest technology of DOnetworks, was developed to acquire the highest quality of the telephonic communication. DOFree improves your ability to hear conversations clearly even in noisy environments.

Automatic stand-by mode

30 seconds after you finish talking, DOFree Bluetooth headset turns to stand-by mode automatically to prevent the draining the battery.

Volume controlling by one-touch

The volume control button locate upper in front of the headset, hence the user may start conversation, control the volume without touching the cell-phone itself. A separate volume control lets you raise($\triangle$) and lower(∇) the call volume as you move from place to place-from bedroom to boardroom, cafe to conference, or presentation to party.

Compatibility with Non Bluetooth cell-phone

The Dongle of DOnetworks enables to use the Bluetooth headset for the non Bluetooth cell-phone user. The Dongle is ultra lightweight, micro-sized, stylish designed.

Designed for both ears

It may be worn on either ear for any circumstances.

Safe High-Capacity Li-ion Polymer Battery used

The latest High-technology Li-ion Polymer battery helps reduce the unit's size.

It is not harmful to humans, and can be used for a longer time.

*** How to use**

1.Preparing the kit for use.

- Plug in the adaptor to a wall socket.
- Place the Headset and Dongle(Audio Gateway) of Adaptor Jack into the Adaptor.

2.Please charge the Headset and Dongle(Audio Gateway) fully for at least 3 hours.

- LED lamps of the Headset and Dongle(Audio Gateway) will indicate charging status.
- No light: Fully charged.
- Red light: Charging in process.

3.Using with a cellular phone.

■ Making a phone call.

- At First Press Talk Button(☎) of the Headset for 2 to 3 seconds.
 - Green light : A flicking light when the headset or the Dongle(Audio Gateway) is ON.
- Confirm ON status by checking that the LED lamp of the Headset and Press On/OFF Switch of the Dongle(Audio Gateway).
- Connect the ear plug of the Dongle(Audio Gateway) into the earphone jack of a cellular phone.
- Dial a number using the keypad of the cellular phone, then press TALK(or CALL) button. The Talk button(☎) on the Headset can be used to dial out the number entered into the cellular phone on some models.

■ Receiving a Phone call.

- Press the TALK (or CALL) button on the cellular phone or press the Hook button on the Headset.

■ Ending a Phone call.

- Press the END button (or the appropriate button to end a call) on the cellular phone or press the Talk button(☎) again on the Headset for 2~ 3 seconds.

■ Redial Feature.

- Some cellular phones with Redial feature can utilize the Talk button(☎) on the Headset to redial the last number dialed from the cellular phone.
 - Press the Talk button(☎) once. The display on the cellular phone will show the last dialed number. Press Talk button(☎) again to dial that number.
- ※ Note: These features may not be available on all cellular phones.