

This device using e-label, please refer to page 16 of the user manual.

7.0 Regulation and Compliance

BT-30 complies of different regulation and standard. You can find the information of regulation by tapping the setting icon  and then selecting the “Regulation and Compliance”. For more details, please visit our website www.ectherm.com.





Figure 23. Regulation and Compliance

A	B
2D FILE PATH	
平面图路径	

E			F			
SYM	DATE	ECN NO	DESCRIPTION	MODIFY	APPR.	REV



CHARGE BOTTOM CASE 印字图

注：黑底及外形方框请不用理会, 仅需印字即可

备注:

- 1) 产品不能有严重拔锋、缩水、流痕、顶白、变形等不良现象。
- 2) 未注拔模不小于1°。
- 3) 水口剪切处不可有明显发白现象。
- 4) □□内为重点控制尺寸。
- 5) 2D图未注尺寸以3D为准。

备注: 1) 产品不能有严重披锋、缩水、流痕、顶白、变形等不良现象。 2) 未注披锋不小于1° 3) 水口剪切处不可有明显发白现象。 4) □ 内为重点控制尺寸, 5) 2D图未注尺寸以3D为准。	THIS DRAWING USED OF		GENERAL TOLERANCE 通用公差				MANFORD		1		CHANGE BOTTOM CASE			
	本 图 适 用 于		0~10mm	10~50mm	60~120mm	120~400mm	CUSTOMER 客户	FINISHING & TREATMENT 加工及表面处理	QTY数量	PART NO 产品编号	PO# NO 订单编号	TITLE 名称		
			±0.1	±0.20	±0.30	±0.40								
			400~500mm	600~1000mm	ANGLE:									
			±0.5	±0.8	±1.0°									
			DON'T COPY WITHOUT ALLOWED OF LKWA		APPROVED 批准	CHECKED 审核								CHECKED 审核
	未经 LKWA 工程面许可, 不得复印													
	3RD.ANGLE'S													
														
	A	B	C	D				E		F				
FM-MOD-001-														