



Tron 40AIS
EPIRB

ENABLED

1000

JUL 2021
00070
974010070

JOTRON

RLS
TEST

PUSH

Class 2
Frequency: 121.5 to 157.5 (147 to 157.5)
Wavelength: 1900 to 1875 (1875 to 1887.5)

Operating distance:
Automatic activation: 1000 m
Manual activation: 1000 m
Maximum range: 1000 m


Activation: Push the red tab and ensure it goes to the ON position

Deactivation: Take the EPIRB out of water and move the switch to the OFF position

USE ONLY IN EMERGENCY

Normal test: Move switch to the ON position and hold for 5 s. Top light flash = OK

Extended test (ON/OFF): Move switch to the OFF position twice within 5 s. Top light flash = OK



Manual activation
1) Pull the red tab
2) Push the switch, and ensure it goes to ON

Automatic activation
The EPIRB will automatically be activated in water

Deactivation
Take the EPIRB out of water, and move the switch to the OFF position

USE ONLY IN EMERGENCY



Normal test
Move switch to the ON position and hold for 5 s. Top light flash = OK

Extended test (ON/OFF)
Move switch to the OFF position twice within 5 s. Top light flash = OK